

## W26FX001 Temendous E0026

The extremely stiff cone made from aluminium/magnesium alloy gives tremendous bass precision.


2" diameter high temperature voice coil with black anodized aluminium coil former for high power handling and reduced power compression.

Heavy copper rings mounted above and below the T-shaped pole piece reduce non linear and modulation distortion and increase overload margin.

Extremely stiff and stable injection moulded metal basket keeps the critical components in perfect alignment. Large windows in the basket both above and below the spider reduce sound reflexion, air flow noise and cavity resonance to a minimum.


A solid copper phase plug enhances the performance of the copper rings and improves heat conduction away from the pole piece.

Gold plated terminals mounted on a glass fibre reinforced plate to reduce contact resistance and improve reliability.



The frequency responses above show measured free fields ound pressure in 0, 30, and 60 degrees angle using a 28L closed box. Input 2.83 VRMs, microphone distance 0.5m, normalized to SPL 1m. The dotted line is a calculated response in infinite baffle based on the parameters given for this specific driver. The impedance is measured in free air without baffle using a 2V sine signal.





Nominal Impedance	8 Ohms	Voice Coil Resistance	6.3 Ohms
Recommended Frequency Range	20 - 1000 Hz	Voice Coil Inductance	1.43 mH
Short Term Power Handling *	400 W	Force Factor	10.7 N/A
Long Term Power Handling *	150 W	Free Air Resonance	20 Hz
Characteristic Sensitivity (2,83V, 1m)	87 dB	Moving Mass	56.3 g
Voice Coil Diameter	51 mm	Air Load Mass In IEC Baffle	3.48 g
Voice Coil Height	20 mm	Suspension Compliance	1.1 mm/N
Air Gap Height	6 mm	Suspension Mechanical Resistance	3.21 Ns/m
Linear Coil Travel (p-p)	14 mm	Effective Piston Area	330 cm <sup>2</sup>
Maximum Coil Travel (p-p)	35 mm	VAS	162 Litres
Magnetic Gap Flux Density	1.23 T	QMS	2.34
Magnet Weight	1.30 kg	QES	0.41
Total Weight	4.20 kg	QTS	0.35

Jul 2007-1 \*IEC 268-5 EW26-001
SEAS reserves the right to change technical data

RoHS compliant product www.seas.no